N / - 4 | - - - |

PR48-Clear Clear Prototyping Material

General Information

PR48 is formulated to work with DLP and SLA 3D printers using 385-405 nm light. It is specifically tuned to print on the Autodesk Ember printer. PR48 will extend the window lifetime of the Ember and other printers that use PDMS windows. This resin reliably produces clear prints with good positive and negative resolution.

Chemical Data

\/° • • • • • • • • • • • • • • • •			Method
Viscosity (cps	400		Brookfield SP #31
@25 °C			
	Fresh Print	Post-cured	
Tensile Modulus	600	1400	ASTM D 638-14
(mPa) Tensile Strength	16	28	ASTM D 638-14
(mPa) Elongation	_		
(%)	5	3	ASTM D 638-14

^{*}Parts were post-cured for 10min a side with a broad spectrum UV light at 30mW/cm2.

Post Cure Procedure

Parts should be post cured under a broad band, UV light for 10 minutes on a side at 30 mW/cm² to bring the parts up to their full properties

Arkema Inc., 3D Printing Development Center 1880 S. Flatiron Ct STE J, Boulder, CO 80301



^{*}Properties may vary in orientation and post-treatment.